

GRAS 45CA

Headphone/Hearing-protector Test Fixture



ISO: 4869-3
IEC: 60318-1 and 60318-4
depending on configuration

The GRAS 45CA is a versatile test fixture for measuring sound isolation of hearing-protectors according to ISO 4869-3 and ear- and headphones according to IEC60318-1 or 60318-4. For testing hearing-protectors according to ANSI/ASA S12.42, choose [GRAS 45CB](#).



ES France - Département Tests & Mesures
127 rue de Buzenval BP 26 - 92380 Garches



Tél. 01 47 95 99 45



e-mail : tem@es-france.com
Site Web : www.es-france.com

Introduction

GRAS 45CA provides the basis for reliable and exact measurements and is designed with

- A test fixture mounted on a resilient base that reduces the noise floor to a minimum in a typical test situation. Foam plugs and grease are supplied to avoid sound leakage along the cable
- A test fixture head, made for optimizing the acoustic isolation
- An acoustic cup and plug for testing the acoustic isolation
- A range of molded-rubber KEMAR pinnae, e.g. for testing earplugs, can be fitted

The 45CA's robust design is ideally suited for binaural testing of active and passive earplugs, as well as circumaural hearing protectors.

It is primarily intended for testing the performance of hearing-protection devices such as earplugs and earmuffs (supra-aural and circum-aural) but can also be used for testing sound sources such as earphones and headphones. It is fitted with either microphones or ear simulators, depending on the device to test and the standard to comply with.

Compliance with ISO 4869-3, IEC 60318-1, and IEC 60318-4 assures technicians, decision-makers, and authorities of repeatability and transparent data when developing and verifying hearing protectors.

The pinnae for the 45CA are the same as the standardized KEMAR pinnae but rounded to fit the large 45CA base plate. This large base plate reduces or eliminates the risk of leakage.

The 45CA includes two plugs for measuring the acoustic isolation in a closed ear.

We recommend calibration before each use to ensure the accuracy of your measurements. The [GRAS 42AP](#) Intelligent Pistonphone or the [GRAS](#)

[42AA](#) Pistonphone are ideally suited for this task.

TEDS Compatibility

All CCP-based configurations (-2, -4, -6, -8, -10 and -12) are IEEE 1451.4 TEDS v. 1.0 compliant. If your measurement platform supports Transducer Electronic Data Sheets (TEDS), you will be able to read and write data like properties and calibration data.

Configurations for typical applications and use

45CA Headphone/Hearing-protector Test Fixture, Non-configured is a versatile test platform that you can configure to suit specific needs. The most common configurations can be ordered fully assembled, calibrated and tested from GRAS These are:

45CA-1 Headphone/Hearing-protector Test Fixture, ISO 4869-3 1" Mic. LEMO

The 45CA-1 is a configuration for testing outside-the-ear devices, i.e. for measuring the insertion loss of earmuffs and the sound quality of headphones. In this configuration, 45CA is configured with two GRAS 40EN 1" pressure microphones. **Configured according to ISO 4869-3.**

45CA-2 Headphone/Hearing-protector Test Fixture, ISO 4869-3 1/2" Mic. CCP

The 45CA-2 is a configuration for testing outside-the-ear devices, i.e., for measuring the insertion loss of earmuffs and the sound quality of headphones. In this configuration, 45CA is configured with two GRAS 40AD 1/2" pressure microphones. **Configured according to ISO 4869-3.**

45CA-3 Headphone/Hearing-protector Test



Fixture, IEC 60318-1 LEMO

45CA-3 is configured for measurement of insertion loss of circum-aural hearing protectors and the sound quality of headphones, with two RA0039 Ear Simulators with 40AG 1/2" externally polarized microphones. The RA0039 cannot be used with a pinna simulator and therefore cannot be used for measuring in-ear earphones. **The configuration complies with IEC 60318-1.**

45CA-4 Headphone/Hearing-protector Test Fixture, IEC 60318-1 CCP

The 45CA-4 is configured with two RA0039 Ear Simulators with 40AO 1/2" prepolarized microphones and is used for measurements of insertion loss of circum-aural hearing protectors and sound quality of headphones. The RA0039 cannot be used with a pinna simulator and therefore cannot be used for measuring in-ear earphones. **The configuration complies with IEC 60318-1.**

45CA-5 Headphone/Hearing-protector Test Fixture, IEC 60318-4 LEMO

The 45CA-5 is configured with RA0045 externally polarized ear simulators for use with pinna simulators. It can be used for measurements of the insertion loss of earmuffs and earplugs, and the sound quality of earphones and headphones. **The configuration complies with IEC 60318-4. Insertion loss performing according to ISO 4869-3.**

45CA-6 Headphone/Hearing-protector Test Fixture, IEC 60318-4 CCP

The 45CA-6 is configured with RA0045-S1 prepolarized ear simulators for use with pinna simulators. This configuration can be used for measurements of the insertion loss of earmuffs, sound quality of earphones and hearing aids. **The**

configuration complies with IEC 60318-4. Insertion loss performing according to ISO 4869-3.

45CA-7 Headphone/Hearing-protector Test Fixture, IEC 60318-4 LEMO, with Anthropometric Pinnae

The 45CA-7 is configured with RA0045 externally polarized ear simulators and anthropometric pinnae. It can be used for measurements of the insertion loss of earmuffs and earplugs, and the sound quality of earphones and headphones. **The configuration complies with IEC 60318-4. Insertion loss performing according to ISO 4869-3.**

45CA-8 Headphone/Hearing-protector Test Fixture, IEC 60318-4 CCP, with Anthropometric Pinnae

The 45CA-8 is configured with RA0045-S1 prepolarized ear simulators and anthropometric pinnae. This configuration can be used for measurements of the insertion loss of earmuffs, sound quality of earphones and hearing aids. **The configuration complies with IEC 60318-4. Insertion loss performing according to ISO 4869-3.**

45CA-9 Headphone/Hearing-protector Test Fixture, High-Frequency Ear Simulator, and Anthropometric Pinnae, LEMO

The 45CA-9 is configured with RA0401 externally polarized high-frequency ear simulators and anthropometric pinnae. It can be used for measurements of hearing aids, earphones, and headphones up to 20 kHz. **The configuration complies with IEC 60318-4. Insertion loss performing according to ISO 4869-3.**

45CA-10 Headphone/Hearing-protector Test Fixture, High-Frequency Ear Simulator and Anthropometric Pinnae, CCP

The 45CA-10 is configured with RA0402 prepolarized ear simulators and anthropometric pinnae. It can be used for measurements of hearing aids, earphones, and headphones up to 20 kHz. **The configuration complies with IEC 60318-4. Insertion loss performing according to ISO 4869-3.**

45CA-11 Headphone/Hearing-protector Test Fixture, Hi-Res Ear Simulator and Anthropometric Pinnae, LEMO

The 45CA-11 is configured with RA0403 externally polarized hi-res ear simulators and anthropometric pinnae. It can be used for measurements of hearing aids, earphones and headphones up to 50 kHz. **The configuration complies with IEC 60318-4. Insertion loss performing according to ISO 4869-3.**

45CA-12 Headphone/Hearing-protector Test Fixture, Hi-Res Ear Simulator and Anthropometric Pinnae, CCP

The 45CA-12 is configured with RA0404 prepolarized hi-res ear simulators and anthropometric pinnae. It can be used for measurements of hearing aids, earphones, and headphones up to 50 kHz. **The configuration complies with IEC 60318-4. Insertion loss performing according to ISO 4869-3.**

45CA-13 Headphone/Hearing-protector Test Fixture, Low Noise Ear Simulator System

The 45CA-13 is configured with 43BB low noise ear simulator systems and anthropometric pinnae. It can be used for measurements of hearing aids, earphones, and headphones. **The configuration**

complies with IEC 60318-4. Insertion loss performing according to ISO 4869-3.

The application-specific items for each of these configurations are listed under the tab Ordering Information.

System verification

For daily verification and check of your measurement setup, we recommend using a calibrator like [GRAS 42AG](#) Multifunction Sound Calibrator. For proper sensitivity calibration, we recommend using a pistonphone like [GRAS 42AP](#) Intelligent Pistonphone.

Service

If you accidentally damage the Ear Simulator, we can—in most cases—replace and repair it at a very reasonable cost and with short turn-around time. This not only protects your investment but also pleases your quality assurance department because you don't have to worry about new serial numbers, etc.

Calibration

Before leaving the factory, all products are calibrated in a controlled laboratory environment using traceable calibration equipment. Depending on the use, measurement environment, and internal quality control programs, we recommend recalibrating the system at least once a year.

Performance and warranty

The GRAS 45CA is made of components from our standard portfolio and are all manufactured of high-quality material and branded parts that were chosen and processed to ensure life-long stability and robustness. This enables us to offer 5 years warranty against defective materials and workmanship.

Exceptions: The warranty period for cables is 6



months.



IEC standard		Dep. on conf.
ITU-T recommendations		P.380
CE/RoHS compliant/WEEE registered		Yes/Yes/Yes
Weight	g / oz	11.6 k / 409.18

45CA-1 and 45CA-2

Self Insertion Loss, measured with closed ear simulators	> 50 dB	80 - 250 Hz
Self Insertion Loss, measured with closed ear simulators	> 65 dB	350 - 4000 hz
Self Insertion Loss, measured with closed ear simulators	> 55 dB	5000 - 20000 Hz
Specs for the GRAS 40EN 1" Externally Polarized Pressure Microphone can be found here .		
Specs for the GRAS 40AD 1/2" Prepolarized Pressure Microphone can be found here .		

45CA-3 and 45CA-4

GRAS RA0039 Ear Simulator	Specs can be found here :	www.gras.dk/RA0039
GRAS 40AG 1/2" Externally Polarized Pressure Microphone	Specs can be found here :	www.gras.dk/40AG
GRAS 40AO 1/2" Prepolarized Pressure Microphone	Specs can be found here :	www.gras.dk/40AO

45CA-5 to 45CA-8

GRAS RA0045 Ear Simulator	Specs can be found here :	www.gras.dk/RA0045
GRAS RA0045-S1 Ear Simulator	Specs can be found here :	www.gras.dk/RA0045-s1

45CA-9 to 45CA-10

GRAS RA0401 High-Frequency Ear Simulator Externally Polarized	Specs can be found here :	www.gras.dk/RA0401
GRAS RA0402 High-Frequency Ear Simulator Prepolarized	Specs can be found here :	www.gras.dk/RA0402

45CA-11 to 45CA-12

GRAS RA0403 Hi-Res Ear Simulator Externally Polarized	Specs can be found here :	www.grasacoustics.com/ra0403
---	---	--



GRAS RA0404 Hi-Res Ear Simulator Prepolarized

Specs can be found
[here:](#)

www.grasacoustics.com/ra0404

45CA-13

GRAS 43BB Ear Simulator

Specs can be found
[here:](#)

www.grasacoustics.com/43bb

GRAS Sound & Vibration reserves the right to change specifications without notice.



Included items with GRAS 45CA

Common to all configurations - and delivered when ordered non-configured

GRAS GR1085	Cover Plate, 2 pcs
GRAS GR0970	Insert
GRAS GR0974	Acoustic Cup (for acoustic isolation testing)
GRAS RA0178	1" Acoustic Plug
GRAS GR1281	Foam plug for leakage sealing (2 pcs)
GRAS MI0016	7 ml Silicon grease for leakage sealing
GRAS YY0019	Allen Key, 6 mm
GRAS YY0016	Allen Key, 2.5 mm
GRAS YY0018	Allen Key, 2 mm
GRAS YY0012	Allen Key, 1.5

Configurations

12 different pre-configurations of 45CA are available. Each of these are sold fully assembled and tested, ready for use.

45CA-1 1" Headphone/Hearing-Protector Test Fixture, ISO 4869-3 1" Mic. LEMO - for test of earmuffs

GRAS 40EN	1" Ext. Polarized Pressure Microphone (2 pcs)
GRAS RA0017	Adapter for 1" microphone and 1/2" preamplifier (2 pcs)
GRAS RA0003	Adapter for 1/2" microphone and 1/4" preamplifier (2 pcs)
GRAS 26AS	1/4" Standard Preamplifier with 3 m integrated cable, very short (2 pcs)

45CA-2 1/2" Headphone/Hearing-Protector Test Fixture, ISO 4869-3 1/2" Mic. CCP - for test of earmuffs

GRAS 40AD	1/2" Pre-polarized Pressure Microphone, High Sensitivity (2 pcs)
GRAS RA0177	1" Microphone protection grid (2 pcs)



GRAS RA0058	1/2" to 1" Microphone Adapter (2 pcs)
GRAS GR0010	1/2" to 1/4" Adapter (2 pcs)
GRAS 26CB	1/4" CCP Preamplifier with Microdot connector, very short (2 pcs)
GRAS AA0070	3 m Microdot - BNC Cable, High Temp

45CA-3 Headphone/Hearing-Protector Test Fixture, IEC 60318-1 LEMO - for test of earmuffs and headphones

GRAS RA0039	Ear Simulator according to IEC 60318-1 (2 pcs)
GRAS 40AG	1/2" Ext. Polarized Pressure Microphone (2 pcs)
GRAS RA0176	1/2" to 1" Adapter for RA0039 (2 pcs)
GRAS GR0010	1/2" to 1/4" Adapter (2 pcs)
GRAS 26AS	1/4" Standard Preamplifier with 3 m integrated cable, very short (2 pcs)

45CA-4 Headphone/Hearing-Protector Test Fixture, IEC 60318-1 CCP - for test of earmuffs and headphones

GRAS RA0039	Ear Simulator according to IEC 60318-1 (2 pcs)
GRAS 40AO	1/2" Prepolarized Pressure Microphone (2 pcs)
GRAS RA0176	1/2"-1" Adapter for RA0039 (2 pcs)
GRAS GR0010	1/2" to 1/4" Adapter (2 pcs)
GRAS 26CB	1/4" CCP Preamplifier with Microdot connector, very short (2 pcs)
GRAS AA0070	3 m Microdot - BNC Cable, High Temp

45CA-5 Headphone/Hearing-Protector Test Fixture, IEC 60318-4 LEMO - for test of earmuffs, earplugs, headphones and earphones

GRAS KB0070	Large Right KEMAR Pinna, 55 Shore 00
GRAS KB0071	Large Left KEMAR Pinna, 55 Shore 00
GRAS GR1075	Pinna Holder Plate

GRAS GR1069	Ear Canal Extension
GRAS RA0045	Externally Polarized Ear Simulator according to IEC 60318-4 (60711) (2 pcs)
GRAS GR0010	1/2" to 1/4" Adapter (2 pcs)
GRAS 26AS	1/4" Standard Preamplifier with 3 m integrated cable, very short (2 pcs)

45CA-6 Headphone/Hearing-Protector Test Fixture, IEC 60318-4 CCP - for test of earmuffs, earplugs, headphones and earphones

GRAS KB0070	Large Right KEMAR Pinna, 55 Shore 00
GRAS KB0071	Large Left KEMAR Pinna, 55 Shore 00
GRAS GR1075	Pinna Holder Plate
GRAS GR1069	Ear Canal Extension
GRAS RA0045-S1	Prepolarized Ear Simulator according to IEC 60318-4 (60711) (2 pcs)
GRAS GR0010	1/2" to 1/4" Adapter (2 pcs)
GRAS 26CB	1/4" CCP Preamplifier with Microdot connector, very short (2 pcs)
GRAS AA0070	3 m Microdot - BNC Cable, High Temp (2 pcs)

45CA-7 Headphone/Hearing-Protector Test Fixture, IEC 60318-4 LEMO, with Anthropometric Pinnae - for test of earmuffs, earplugs, headphones and earphones

GRAS KB5010	Large Right Anthropometric KEMAR Pinna 35 Shore 00
GRAS KB5011	Large Left Anthropometric KEMAR Pinna 35 Shore 00
GRAS GR1075	Pinna Holder Plate
GRAS RA0045	Externally Polarized Ear Simulator according to IEC 60318-4 (60711) (2 pcs)
GRAS GR0010	1/2" to 1/4" Adapter
GRAS 26AS	1/4" Standard Preamplifier with 3 m integrated cable, very short (2 pcs)
GRAS GR0408	Exterior Ear Canal (for calibration)
GRAS GR0409	Union Nut (for calibration)

45CA-8 Headphone/Hearing-Protector Test Fixture, IEC 60318-4 CCP, with Anthropometric Pinnae - for test of earmuffs, earplugs, headphones and earphones

GRAS KB5010	Large Right Anthropometric KEMAR Pinna 35 Shore 00
GRAS KB5011	Large Left Anthropometric KEMAR Pinna 35 Shore 00
GRAS GR1075	Pinna Holder Plate
GRAS RA0045-S1	Prepolarized Ear Simulator according to IEC 60318-4 (60711) (2 pcs)
GRAS GR0010	1/2" to 1/4" Adapter
GRAS 26CB	1/4" CCP Preamplifier with Microdot connector, very short (2 pcs)
GRAS AA0070	3 m Microdot - BNC Cable, High Temp (2 pcs)
GRAS GR0408	Exterior Ear Canal (for calibration)
GRAS GR0409	Union Nut (for calibration)

45CA-9 Headphone/Hearing-Protector Test Fixture, High-Frequency Ear Simulator with Anthropometric Pinnae, LEMO - for test of headphones and earphones up to 20 kHz

GRAS KB5010	Large Right Anthropometric KEMAR Pinna 35 Shore 00
GRAS KB5011	Large Left Anthropometric KEMAR Pinna 35 Shore 00
GRAS GR1075	Pinna Holder Plate
GRAS RA0401	Externally Polarized High-Frequency Ear Simulator (2 pcs)
GRAS GR0010	1/2" to 1/4" Adapter
GRAS 26AS	1/4" Standard Preamplifier with 3 m integrated cable, very short (2 pcs)
GRAS GR0408	Exterior Ear Canal (for calibration)
GRAS GR0409	Union Nut (for calibration)

45CA-10 Headphone/Hearing-Protector Test Fixture, High-Frequency Ear Simulator with Anthropometric Pinnae, CCP - for test of headphones and earphones up to 20 kHz

GRAS KB5010	Large Right Anthropometric KEMAR Pinna 35 Shore 00
GRAS KB5011	Large Left Anthropometric KEMAR Pinna 35 Shore 00

GRAS GR1075	Pinna Holder Plate
GRAS RA0402	Prepolarized High-Frequency Ear Simulator (2 pcs)
GRAS GR0010	1/2" to 1/4" Adapter
GRAS 26CB	1/4" CCP Preamplifier with Microdot connector, very short (2 pcs)
GRAS AA0070	3 m Microdot - BNC Cable, High Temp (2 pcs)
GRAS GR0408	Exterior Ear Canal (for calibration)
GRAS GR0409	Union Nut (for calibration)

45CA-11 Headphone/Hearing-Protector Test Fixture, Hi-Res Ear Simulator with Anthropometric Pinnae, LEMO - for test of headphones and earphones up to 50 kHz

GRAS KB5010	Large Right Anthropometric KEMAR Pinna 35 Shore 00
GRAS KB5011	Large Left Anthropometric KEMAR Pinna 35 Shore 00
GRAS GR1075	Pinna Holder Plate
GRAS RA0403	Externally Polarized Hi-Res Ear Simulator (2 pcs)
GRAS 26AS	1/4" Standard Preamplifier with 3 m integrated cable, very short (2 pcs)
GRAS GR0408	Exterior Ear Canal (for calibration)
GRAS GR0409	Union Nut (for calibration)

45CA-12 Headphone/Hearing-Protector Test Fixture, Hi-Res Ear Simulator with Anthropometric Pinnae, CCP - for test of headphones and earphones up to 50 kHz

GRAS KB5010	Large Right Anthropometric KEMAR Pinna 35 Shore 00
GRAS KB5011	Large Left Anthropometric KEMAR Pinna 35 Shore 00
GRAS GR1075	Pinna Holder Plate
GRAS RA0404	Prepolarized Hi-Res Ear Simulator (2 pcs)
GRAS 26CS	1/4" CCP Preamplifier with Microdot connector, very short (2 pcs)
GRAS AA0070	3 m Microdot - BNC Cable, High Temp (2 pcs)
GRAS GR0408	Exterior Ear Canal (for calibration)
GRAS GR0409	Union Nut (for calibration)

Optional accessories

KEMAR Pinnae for configurations with using IEC 60318-4 Ear Simulator

GRAS RA0172	Pinna & Ear Simulator Mounting Kit (required to hold a pinna) Included with 45CA-5 and -6. Note: Contains a cover plate, ear canal extension, screws and Allen key
GRAS KB0070	KEMAR Large Right Pinna Shore 55 Hearing Protector. Included with 45CA-5 and 6.
GRAS KB0071	KEMAR Large Left Pinna Shore 55 Hearing Protector. Included with 45CA-5 and 6.
GRAS KB1070	KEMAR Large Right Pinna Shore 35 Hearing Protector
GRAS KB1071	KEMAR Large Left Pinna Shore 35 Hearing Protector
GRAS KB0072	KEMAR Small Right Pinna Shore 55 Hearing Protector
GRAS KB0073	KEMAR Small Left Pinna Shore 55 Hearing Protector
GRAS KB5010	KEMAR Large Right Anthropometric Pinna for 45CA, Shore 35. Included with 45CA-7 and 8
GRAS KB5011	KEMAR Large Left Anthropometric Pinna for 45CA, Shore 35. Included with 45CA-7 and 8

Cables for LEMO configurations

GRAS AA0008	3 m LEMO 7-pin - LEMO 7-pin Cable
GRAS AA0009	10 m LEMO 7-pin - LEMO 7-pin Cable

Cables for CCP configurations

GRAS AA0035	3 m BNC - BNC Cable
GRAS AA0037	10 m BNC - BNC Cable
GRAS AE0074	BNC - BNC adapter

Power modules

GRAS 12AQ	For all configurations (dual channel LEMO/CCP)
GRAS 12AA	For externally polarized configurations only (dual channel)

Power Supply +15 VDC (provides +15 VDC power to the Power Module)

GRAS AB0002	Mains/line power supply, 230 VAC (EU mains connector)
GRAS AB0006	Mains/line power supply, 230 VAC (UK mains connector)
GRAS AB0003	Mains/line power supply, 120 VAC (US mains connector)

Calibration Equipment

GRAS 42AP	Intelligent Pistonphone, Class 0
GRAS 42AA	Pistonphone, Class 1
GRAS RA0023	Coupler for 1" microphones (Note: RA0023 is included with 42AP but optional for 42AA)
GRAS RA0287	Calibration Adapter (for in-situ verification of RA0039)
GRAS RA0157	1/2" Calibration Adapter for KEMAR Pinna (For the IEC60318-4 configuration only)
GRAS 42AG	Multifunction Sound Calibrator, Class 1

GRAS Sound & Vibration reserves the right to change accessories without notice.

GRAS Worldwide

Subsidiaries and distributors in more than 40 countries

HEAD OFFICE, DENMARK

GRAS SOUND & VIBRATION

Skovlytoften 33
2840 Holte
Denmark
Tel: +45 4566 4046
www.GRASacoustics.com
gras@grasacoustics.com

USA

GRAS SOUND & VIBRATION

9290 SW Nimbus Avenue
Beaverton, OR 97008
Tel: 503-627-0832
Toll Free: 800-231-7350
www.GRASacoustics.com
sales-usa@grasacoustics.com

UK

GRAS SOUND & VIBRATION

Unit 115, Gibson House,
Ermine Business Park, Huntingdon,
Cambridgeshire, PE29 6XU
Tel: +44 (0) 7762 584 202
www.GRASacoustics.com
sales-uk@grasacoustics.com

CHINA

GRAS SOUND & VIBRATION

Room 315, RuiBo Center(T1)
Lane683, Shenhong Rd,
Minhang District,
Shanghai, China, 201107
Tel: +86 21 64203370
www.GRASacoustics.cn
cnsales@grasacoustics.com



About GRAS Sound & Vibration

GRAS is a worldwide leader in the sound and vibration industry. We develop and manufacture state-of-the-art measurement microphones and related equipment for industries where acoustic measuring accuracy and repeatability are of the utmost importance. This includes applications and solutions for customers within the fields of aerospace, automotive, audiology, consumer electronics and other highly demanding industries. GRAS microphones are designed to live up to the high quality, durability and accuracy that our customers have come to expect, trust and require.

GRAS Sound & Vibration is represented through subsidiaries and distributors in more than 40 countries and is part of Axiometrix Solutions, a leading test solutions provider comprised of globally recognized measurement brands. Read more at www.grasacoustics.com

grasacoustics.com

GRAS
An Axiometrix Solutions Brand



ES France - Département Tests & Mesures
127 rue de Buzenval BP 26 - 92380 Garches



Tél. 01 47 95 99 45



e-mail : tem@es-france.com
Site Web : www.es-france.com