

DVE™ Viscometer

our most affordable digital viscometer

New User Interface

- Keypad control
- Sharp viewing screen for close up or distance viewing

No Calculations Required

- Direct reading of viscosity

Displayed Info:

- Viscosity (cP, P, mPa•s or Pa•s)
- % Torque
- Speed/Spindle

Easy-to-Use

Range:

Push for determining full scale range (FSR) viscosity

18 Speeds

for complete range capability

Bubble Level

conveniently located for easy adjustment

Accuracy: $\pm 1.0\%$ of range

Repeatability: $\pm 0.2\%$



What's Included?

Instrument
6 spindles (RV/HA/HB)
or 4 spindles (LV)
Spindle Guard Leg*
Lab Stand (Model A)
Carrying Case

*Not applicable to HA or HB torque models

Optional Accessories

Viscosity Standards
RV/HA/HB-1 Spindle
Quick Action Lab Stand
Temperature Bath
Small Sample Adapter
UL Adapter
Thermosel
DIN Adapter
Quick Connect/Extension Links

MODEL	VISCOSITY RANGE cP(mPa•s)		SPEEDS	
	Min.	Max.	RPM	Number of Increments
DVELV	1†	2M	.3-100	18
DVERV	100††	13M	.3-100	18
DVEHA	200††	26M	.3-100	18
DVEHB	800††	104M	.3-100	18

† 1 cP achieved with UL Adapter accessory. 15 cP on LV with standard spindles.

†† Minimum viscosity is achieved with optional RV/HA/HB-1 spindle.

M = 1 million cP = Centipoise mPa•s = Millipascal•seconds

